



Low Profile Wall LED

PW15-NW-G1-8-BZ

Low Profile Wall, LED, 15W, 4000K, 70 CRI, 120-277V, Bronze - 110 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

Product data

General Information		DesignLights Consortium Qualified Product List	
Lamp Source Code	LED		
Color Temperature	4000K		
CRI	70		
Photometric Distribution Type	Type II		
Mounting	Wall		
B.U.G. Rating	B1U0G0		
Awards	DLC QPL		
Operating and Electrical		Initial Performance (IEC Compliant)	
Voltages	120/208/240/277 V	Luminaire Lumens	1656
Luminaire Input Watts	15	Efficacy	110 lm/W
Mechanical and Housing		Application Conditions	
Shape	Rectangular	Max Ambient Temp	+40 °C
		Min Ambient Temp	-40 °C
Approval and Application		Product Data	
Safety Listing	UL	Order product name	PW15-NW-G1-8-BZ
		EAN/UPC - Product	783352024299
		Order code	PW15-NW-G1-8-BZ
		Local order code	.
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	6
		Material Nr. (12NC)	912401468308

Low Profile Wall LED

Net Weight (Piece)	1.460 kg
Commercial Code	PW15-NW-G1-8-BZ
Catalog Number Description	Low Profile Wall, LED, 15W, 4000K, 70 CRI, 120-277V, Bronze

Quick Ship	Service Smart (2 Days) USA
-------------------	----------------------------

