



# Low Profile Wall LED

## PW30-NW-G1-8-BZ

Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze - 103 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

### Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	3090
Color Temperature	4000K	Efficacy	103 lm/W
CRI	70	<b>Application Conditions</b>	
Mounting	Wall	Max Ambient Temp	+40 °C
B.U.G. Rating	B2U0G1	Min Ambient Temp	-40 °C
Awards	DLC QPL	<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	PW30-NW-G1-8-BZ
Voltages	120/208/240/277 V	EAN/UPC - Product	783352024305
Luminaire Input Watts	30	Order code	912401468309
<b>Mechanical and Housing</b>		Local order code	.
Shape	Rectangular	Numerator - Quantity Per Pack	1
<b>Approval and Application</b>		Numerator - Packs per outer box	6
Safety Listing	UL	Material Nr. (12NC)	912401468309
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List	Net Weight (Piece)	1.760 kg
		Commercial Code	PW30-NW-G1-8-BZ

## Low Profile Wall LED

---

<b>Catalog Number</b>	Description
	Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze
<b>Quick Ship</b>	Service Smart (2 Days) USA

---

