



# Low Profile Wall LED

Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze

Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze - 103 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

## Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	70
Photometric Distribution Type	Asymmetric
Mounting	Wall
B.U.G. Rating	B2U0G1
Awards	DLC QPL
Number Of Pieces	1

Operating and electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	30
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Shape	Rectangular

Enclosure	Metal and Plastic
-----------	-------------------

Approval and application	
Safety Listing	UL
Energy Certifications	DLC Standard

Initial performance (IEC compliant)	
Luminaire Lumens	3090
Efficacy	103 lm/W

Application conditions	
Ambient temperature range	-40 to +40 °C
Max Ambient Temp	+40 °C
Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C

Product data	
Order product name	PW30-NW-G1-8-BZ

# Low Profile Wall LED

EAN/UPC - Product	783352024305
Order code	PW30-NW-G1-8-BZ
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912401468309
Net Weight (Piece)	1.760 kg

Catalog Number	PW30-NW-G1-8-BZ
Catalog Number Description	Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze

