



Low Profile Wall LED

PW50-NW-G1-8-BZ

Low Profile Wall, LED, 50W, 4000K, 70 CRI, 120-277V, Bronze - 100 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	70
Photometric Distribution Type	Type II
Mounting	Wall
B.U.G. Rating	B2U0G1
Awards	DLC QPL
Operating and Electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	51
Mechanical and Housing	
Shape	Rectangular
Approval and Application	
Safety Listing	UL

DesignLights Consortium Qualified Product List		DesignLights Consortium Qualified Product List
Initial Performance (IEC Compliant)		
Luminaire Lumens	5114	
Efficacy	100 lm/W	
Application Conditions		
Max Ambient Temp	+40 °C	
Min Ambient Temp	-40 °C	
Product Data		
Order product name	PW50-NW-G1-8-BZ	
EAN/UPC - Product	783352024312	
Order code	912401468310	
Local order code	.	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	2	
Material Nr. (12NC)	912401468310	
Net Weight (Piece)	0.100 kg	

Low Profile Wall LED

Commercial Code	PW50-NW-G1-8-BZ
Catalog Number Description	Low Profile Wall, LED, 50W, 4000K, 70 CRI, 120-277V, Bronze

Quick Ship	Service Smart (2 Days) USA
------------	----------------------------

