



# Low Profile Wall LED

## Low Profile Wall, LED, 30W, 4000K, 70 CRI, 347V, Bronze

Low Profile Wall, LED, 30W, 4000K, 70 CRI, 347V, Bronze – 95 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Type II
Mounting	Surface
B.U.G. Rating	BIUOG0
Awards	DLC QPL
Operating and Electrical	
Voltages	347 V
Luminaire Input Watts	17
Mechanical and Housing	
Shape	Rectangular
Approval and Application	
Safety Listing	UL

DesignLights Consortium Qualified Product List	
DesignLights Consortium Qualified Product List	
Initial Performance (IEC Compliant)	
Luminaire Lumens	1655
Efficacy	95 lm/W
Application Conditions	
Max Ambient Temp	+40 °C
Min Ambient Temp	-40 °C
Product Data	
Order product name	PW15-NW-G1-6-BZ
EAN/UPC - Product	783352024329
Order code	PW15-NW-G1-6-BZ
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401468311

# Low Profile Wall LED

Net Weight (Piece)	1.300 kg
Catalog Number	PW15-NW-G1-6-BZ
Catalog Number Description	Low Profile Wall, LED, 30W, 4000K, 70 CRI, 347V, Bronze

