



# Low Profile Wall LED

## Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze

Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze – 95 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	70
Mounting	Surface
B.U.G. Rating	B2U0G1
Awards	DLC QPL
Operating and Electrical	
Voltages	347 V
Luminaire Input Watts	32
Mechanical and Housing	
Shape	Rectangular
Approval and Application	
Safety Listing	UL

DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List
Initial Performance (IEC Compliant)	
Luminaire Lumens	3025
Efficacy	95 lm/W
Application Conditions	
Max Ambient Temp	+40 °C
Min Ambient Temp	-40 °C
Product Data	
Order product name	PW30-NW-G1-6-BZ
EAN/UPC - Product	783352024336
Order code	PW30-NW-G1-6-BZ
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401468312

# Low Profile Wall LED

Net Weight (Piece)	1.500 kg
Catalog Number	PW30-NW-G1-6-BZ
Catalog Number Description	Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze

