



Low Profile Wall LED

Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze

Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze – 93 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

Product data

General Information		DesignLights Consortium Qualified Product List	
Lamp Source Code	LED	DesignLights Consortium Qualified Product List	
Colour Temperature	4000K		
CRI	70		
Photometric Distribution Type	Type II		
Mounting	Surface		
B.U.G. Rating	B2U0G1		
Awards	DLC QPL		
Operating and Electrical		Initial Performance (IEC Compliant)	
Voltages	347 V	Luminaire Lumens	5121
Luminaire Input Watts	55	Efficacy	93 lm/W
Mechanical and Housing		Application Conditions	
Shape	Rectangular	Max Ambient Temp	+40 °C
		Min Ambient Temp	-40 °C
Approval and Application		Product Data	
Safety Listing	UL	Order product name	PW50-NW-G1-6-BZ
		EAN/UPC - Product	783352024343
		Order code	PW50-NW-G1-6-BZ
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401468313

Low Profile Wall LED

Net Weight (Piece)	3.200 kg
Catalog Number	PW50-NW-G1-6-BZ
Catalog Number Description	Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze

