



# Tempo 3 RVP351

## RVP351 SON-TPP250W K IC S

SON-T PIA Plus, 250 W, 255 W, Symmetrical

Tempo is a complete floodlighting range offering a wide choice of lamp types and symmetrical and asymmetrical reflectors. It is designed for general-purpose floodlighting, and is particularly suited to small- to medium-scale area or surface lighting. The Tempo series' compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. A universal mounting bracket allows ceiling, wall or surface mounting with a wide range of adjustment for both down- and uplighting. Tempo's all-weather construction is designed to make cleaning and servicing easy and fast. Access to the lamp and gear is simple, via the hinged front glass with its quick-release stainless-steel clips. All Tempo luminaires are RoHS-compliant.

### Product data

General Information		Standard tilt angle side entry	
Lamp family code	SON-TPP [SON-T PIA Plus]	Standard tilt angle side entry	-
Number of gear units	1 unit	Correlated Color Temperature (Nom)	2000 K
Gear	CONV [Conventional]	Color rendering index (CRI)	25
Glow-wire test	Temperature 850 °C, duration 5 s	Number of light sources	1
Flammability mark	-	Light source color	220 gold
CE mark	Yes	Optical cover type	Flat glass
ENEC mark	-	Luminaire light beam spread	-
Warranty period	1 years	Optic type outdoor	Symmetrical
EU RoHS compliant	Yes	Operating and Electrical	
Light Technical		Input Voltage	230 V
Upward light output ratio	0	Line Frequency	50 Hz
Standard tilt angle posttop	-	Initial CLO power consumption	- W
		End CLO power consumption	{NO} - W

## Tempo 3 RVP351

Inrush current	3.83 A
Inrush time	15 ms
Power Consumption	250 255 W
Power Factor (Fraction)	0.85
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	-

### Temperature

Ambient temperature range	-25 to +35 °C
---------------------------	---------------

### Controls and Dimming

Constant light output	No
-----------------------	----

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	Glass
Fixation material	Steel
Housing Color	Gray
Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	428 mm
Overall width	464 mm
Overall height	146 mm

Effective projected area	0.165 m <sup>2</sup>
Dimensions (Height x Width x Depth)	146 x 464 x 428 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	-
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Power consumption tolerance	+/-7.5%
-----------------------------	---------

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
-------------------------------	-----

### Product Data

Order product name	RVP351 SON-TPP250W K IC S
Full product name	RVP351 SON-TPP250W K IC S
Full product code	871155914975200
Order code	912401483024
Material Nr. (12NC)	912401483024
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559149752
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559149752

