



# Ledinaire Wall-mounted WL060V

## WL060V LED11S/840 PSU II WH

Ledinaire Wall-mounted WL060V, 12.5 W, D285 mm, 1100 lm, 4000 K, IP44

The Philips Ledinaire wall-mounted family has a reputation for simply great LED. The popular, off-the-shelf LED luminaires in this range promise high Philips quality levels at a very competitive price. Reliable, energy-efficient and affordable, Ledinaire WL060V wall-mounted luminaires are designed to cover a wide range of indoor applications from corridors to public entrances. The modern, unobtrusive design also comes in a choice of two sizes and lumen packages, so you can create a uniform look and feel everywhere you need wall-mounted LEDs.

### Product data

General Information			
Light source replaceable	No	Warranty period	3 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
Lighting Technology	LED	EU RoHS compliant	Yes
Value ladder	Value	Light Technical	
CE mark	Yes	Luminous Flux	1,100 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	88 lm/W
		Color rendering index (CRI)	80
		Beam angle of light source	120 degree(s)
		Light source color	840 neutral white

## Ledinaire Wall-mounted WL060V

Optic type	Beam angle 120°
Luminaire light beam spread	120°

### Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	14.5 W
Average CLO power consumption	14.5 W
Inrush current	12.3 A
Inrush time	1.44 ms
Power Consumption	12.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	32

### Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes

### Mechanical and Housing

Housing Material	Acrylonitrile butadiene styrene
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	285 mm
Overall width	285 mm
Overall height	85 mm

Overall diameter	285 mm
Dimensions (Height x Width x Depth)	85 x 285 x 285 mm

### Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance at median useful life* L70	50000 h


### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

### Product Data

Order product name	WL060V LED11S/840 PSU II WH
Full product name	WL060V LED11S/840 PSU II WH
Full product code	871869938232299
Order code	912401483074
Material Nr. (12NC)	912401483074
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699382322
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699382384

## Dimensional drawing



## Ledinaire Wall-mounted WL060V

