

# CoreLine panel

## RC132V LED34S/830 W60L60 IA1 OC

CoreLine panel, 34 W, 600x600 mm, 3400 lm, 3000 K,  
Wireless, Interact Ready, UGR19

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine luminaire panel that works with Interact Pro lighting software and InteractReady devices to provide a connected lighting system for SMEs

### Product data

General Information			
Light source replaceable	No	Embedded control	Interact SNS210 sensor
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on normally flammable surfaces
Connectivity	Interact Ready	ENEC mark	ENEC mark
Lighting Technology	LED	Glow-wire test	Temperature 650 °C, duration 30 s
Value ladder	Performance	EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	3,400 lm
		Correlated Colour Temperature	3000 K
		Luminous efficacy (rated) (nom.)	94 lm/W
		Colour rendering index (CRI)	≥80

CoreLine panel

Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	-
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	19

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	35 W
Inrush current	8 A
Inrush time	0.25 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Wireless
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	597 mm
Overall width	597 mm

Overall height	42 mm
Dimensions (height x width x depth)	42 x 597 x 597 mm

Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L75


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	RC132V LED34S/830 W60L60 IA1 OC
Full product name	RC132V LED34S/830 W60L60 IA1 OC
Full EOC	871869938521700
Order code	38521700
Material no. (12 NC)	912401483128
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699385217
Numerator – packs per outer box	1
EAN/UPC - Case	8718699385217

Dimensional drawing



## CoreLine panel

