



CoreLine panel

RC132V LED34S/830 W60L60 IA1 OC

CoreLine panel, 34 W, 600x600 mm, 3400 lm, 3000 K, Wireless, Interact Ready, UGR19

Philips CoreLine panel Gen5 delivers on the CoreLine promise of innovation, easy installation and excellent illumination. Designed as a direct replacement for functional luminaires in general lighting applications, this LED panel light's innovative MultiLumen feature offers a choice of three lumen packages in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Installing this CoreLine RC132V LED panel is quick and easy too, thanks to a quick connector or Wieland connector. Interact Ready luminaires with integrated wireless communications are also available in this CoreLine range, ready to be used with Interact gateways, sensors and software.

Product data

General Information		Value ladder		Performance	
Light source replaceable	No	Embedded control		Interact SNS210 sensor	
Number of gear units	1 unit	CE mark		Yes	
Driver included	Yes	Warranty period		5 years	
Remarks	*-Per Lighting Europe guidance paper				
	“Evaluating performance of LED based				
	luminaires – January 2018”: statistically				
	there is no relevant difference in lumen				
	maintenance between B50 and for example				
	B10. Therefore, the median useful life (B50)				
	value also represents the B10 value.				
Service tag	Yes	Flammability mark		For mounting on normally flammable	
Connectivity	Interact Ready	ENEC mark		ENEC mark	
Lighting Technology	LED	Glow-wire test		Temperature 650 °C, duration 30 s	
		EU RoHS compliant		Yes	
		Light Technical			
		Luminous Flux		3,400 lm	
		Correlated Color Temperature (Nom)		3000 K	

CoreLine panel

Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	-
Luminaire light beam spread	90°
Unified glare rating CEN	19

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	35 W
Inrush current	8 A
Inrush time	0.25 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Wireless
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	597 mm

Overall width	597 mm
Overall height	42 mm
Dimensions (Height x Width x Depth)	42 x 597 x 597 mm

Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	RC132V LED34S/830 W60L60 IA1 OC
Full product name	RC132V LED34S/830 W60L60 IA1 OC
Full product code	871869938521700
Order code	912401483128
Material Nr. (12NC)	912401483128
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699385217
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699385217

CoreLine panel

Dimensional drawing

