



CoreLine Wall-mounted

WL130V LED12S/840 PSU WH

CoreLine Wall-mounted, 12 W, D350 mm, 1200 lm, 4000 K, IP65

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information			
Lamp family code	LED12 [LED Module 1200 lm]	Warranty period	5 years
Light source replaceable	No	Flammability mark	-
Number of gear units	1 unit	ENEC mark	ENEC mark
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 30 s
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Service tag	Yes	Light Technical	
Lighting Technology	LED	Luminous Flux	1,200 lm
Value ladder	Performance	Correlated Color Temperature (Nom)	4000 K
CE mark	Yes	Luminous Efficacy (rated) (Nom)	100 lm/W
		Color rendering index (CRI)	80
		Beam angle of light source	120 degree(s)
		Light source color	840 neutral white
		Optic type	Opal prismatic reflector
		Optical cover type	Opal bowl with painted cover

CoreLine Wall-mounted

Luminaire light beam spread	120°
-----------------------------	------

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	NA W
Average CLO power consumption	NA W
End CLO power consumption	NA W
Inrush current	12.3 A
Inrush time	1.44 ms
Power Consumption	12 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	32

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Polyamide
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	350 mm
Overall width	350 mm
Overall height	70 mm
Overall diameter	350 mm

Dimensional drawing



Dimensions (Height x Width x Depth)	70 x 350 x 350 mm
-------------------------------------	-------------------

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.39, 0.39) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.7 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* L70	50000 h

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

Product Data

Order product name	WL130V LED12S/840 PSU WH
Full product name	WL130V LED12S/840 PSU WH
Full product code	871869938779299
Order code	912401483183
Material Nr. (12NC)	912401483183
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699387792
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699387976

CoreLine Wall-mounted

