



CoreLine Wall-mounted

WL131V LED12S/830 PSED WH

LED Module 1200 lm - 830 warm white - Power supply unit with DALI interface - White

CoreLine Wall-mounted is a circular-shaped surface-mounted luminaire that is easy to apply in circulation areas such as hallways and staircases. The modern unobtrusive design, in combination with its homogeneous light distribution it delivers, ensures that this luminaire blends into most building architectures. With the push-in connectors, installation is fast and straightforward.

Product data

General Information		Operating and Electrical	
Lamp family code	LED12 [LED Module 1200 lm]	Flammability mark	-
Beam angle of light source	120 °	CE mark	CE mark
Light source color	830 warm white	ENEC mark	ENEC mark
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Constant light output	Yes
Driver/power unit/transformer	Power supply unit with DALI interface	Number of products on MCB of 16 A type B	20
Driver included	Yes	RoHS mark	RoHS mark
Optic type	Opal prismatic reflector		
Optical cover/lens type	Opal bowl with painted cover		
Luminaire light beam spread	120°	Input Voltage	220-240 V
Control interface	DALI	Input Frequency	50 to 60 Hz
Connection	Push-in connector 6-pole	Control signal voltage	0-16 V DC DALI
Cable	-	Initial CLO power consumption	13 W
Protection class IEC	Safety class II	Average CLO power consumption	13 W
Glow-wire test	Temperature 650 °C, duration 30 s	End CLO power consumption	NA W
		Inrush current	22 A

CoreLine Wall-mounted

Inrush time	290 ms
Power Factor (Min)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Material	Polyamide
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Opal
Overall length	350 mm
Overall width	350 mm
Overall height	95 mm
Overall diameter	350 mm
Color	White

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1200 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	90 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	80
Initial chromaticity	(0.44, 0.41) SDCM<3

Initial input power	13 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life	5 %
50000 h	
Median useful life L70B50	50000 h
Median useful life L80B50	38000 h
Median useful life L90B50	18000 h
Lumen maintenance at median useful life*	L70
50000 h	

Application Conditions



Ambient temperature range	-20 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Full product code	871869938792199
Order product name	WL131V LED12S/830 PSED WH
EAN/UPC - Product	8718699387921
Order code	912401483196
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912401483196
Net Weight (Piece)	2.050 kg



Dimensional drawing



CoreLine Wall-mounted WL130V/WL131V

CoreLine Wall-mounted

Photometric data

