



GreenSpace

DN472B LED20S/840 PSE-E C PCC WH

LED Module, system flux 2000 lm - 840 neutral white - Power supply unit external, DC compatible for central emergency lighting - High-gloss mirror - - - Feed-through connector 3-pole - Dust accumulation-protected, splash-proof - White

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information		Emergency lighting	
Number of light sources	1 [1 pc]	Emergency lighting	No [-]
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Connection	Feed-through connector 3-pole
Beam angle of light source	120 °	Cable	-
Light source colour	840 neutral white	Protection class IEC	Safety class II
Cap base	- [-]	Glow-wire test	Temperature 750 °C, duration 5 s
Light source replaceable	No	Flammability mark	F [For mounting on normally flammable surfaces]
Number of gear units	1 unit	CE mark	CE mark
Gear	-	ENEC mark	ENEC mark
Driver/power unit/transformer	PSE-E [Power supply unit external, DC compatible for central emergency lighting]	Warranty period	5 years
Driver included	Yes	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen
Optic type	C [High-gloss mirror]		
Luminaire light beam spread	120°		

	maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	36
RoHS mark	RoHS mark
Unified glare rating CEN	22

Light Technical

Optical cover/lens type accessory	No [-]
-----------------------------------	--------

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	-
Inrush current	15.8 A
Inrush time	0.224 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate aluminium coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall height	94 mm
Overall diameter	216 mm
Colour	White

Approval and Application

Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
-------------------------	---

Mech. impact protection code	IK06 [1 J]
------------------------------	-------------

Initial Performance (IEC Compliant)

Initial luminous flux	2100 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	125 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	80
Initial chromaticity	(0.38, 0.38) SDCM <5
Initial input power	16.8 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions


Ambient temperature range	-15 to +40 °C
Performance ambient temperature Tq	25 °C

Product Data

Full product code	871869938471500
Order product name	DN472B LED20S/840 PSE-E C PCC WH
EAN/UPC – product	8718699384715
Order code	38471500
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	912500100071
Net weight (piece)	1.000 kg





Dimensional drawing



GreenSpace gen2 DN460B-DN473B

Photometric data



IFGU1_DN472BPSE-E1xLED20S840CPCC

IFPC1_DN472BPSE-E1xLED20S840CPCC

