



GreenSpace

DN473B LED20S/830 PSE-E C PCC WH

GreenSpace Compact UGR19 - LED Module, system flux 2000 lm - 830 warm white - Power supply unit external, DC compatible for central emergency lighting - High-gloss mirror - - Feed-through connector 3-pole - Dust accumulation-protected, splash-proof - White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Product data

General information		Optic type	
Number of light sources	1 [1 pc]	Optic type	C [High-gloss mirror]
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Luminaire light beam spread	120°
Beam angle of light source	- °	Emergency lighting	No [-]
Light source colour	830 warm white	Control interface	-
Cap base	- [-]	Connection	Feed-through connector 3-pole
Light source replaceable	No	Cable	-
Number of gear units	1 unit	Protection class IEC	Safety class II
Gear	-	Glow-wire test	Temperature 750 °C, duration 5 s
Driver/power unit/transformer	PSE-E [Power supply unit external, DC compatible for central emergency lighting]	Flammability mark	NO [-]
Driver included	Yes	CE mark	CE mark
		ENEC mark	ENEC mark
		Warranty period	5 years

Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	36
RoHS mark	RoHS mark
Product Family Code	DN471B [GreenSpace Compact UGR19]
Unified glare rating CEN	19

Light Technical

Optical cover/lens type accessory	No [-]
-----------------------------------	--------

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	-
Initial CLO power consumption	- W W
Average CLO power consumption	- W W
Inrush current	15.8 A
Inrush time	0.224 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate aluminium coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall height	94 mm
Overall diameter	216 mm
Colour	White RAL 9003

Approval and Application

Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK06 [1 J]

Initial Performance (IEC Compliant)

Initial luminous flux	1925 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	114 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	>80
Initial chromaticity	(0.44, 0.40) SDCM <5
Initial input power	16.8 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions


Ambient temperature range	-15 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable
Suitable for random switching	Yes

Product Data

Full product code	871869938474600
Order product name	DN473B LED20S/830 PSE-E C PCC WH
EAN/UPC – product	8718699384746
Order code	38474600
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	912500100074
Net weight (piece)	1.000 kg




Dimensional drawing




GreenSpace gen2 DN460B-DN473B

Photometric data



IFGU1_DN473BPSE-E1xLED20S830CPCC



IFPC1_DN473BPSE-E1xLED20S830CPCC

