



# GreenSpace

## DN470T LED20S/840 PSED D22H16 5C6 WH

GreenSpace, 19.2 W, 2225 lm, 4000 K, DALI

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

### Product data

General Information		Light Technical	
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Glow-wire test	Temperature 650 °C, duration 5 s
Cap-Base	- [-]	EU RoHS compliant	Yes
Light source replaceable	No	Luminous Flux	2,225 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	116 lm/W
Lighting Technology	LED	Color rendering index (CRI)	>80
Value ladder	Specification	Number of light sources	1
CE mark	Yes	Light source color	840 neutral white
Warranty period	5 years	Optic type	-
Flammability mark	For mounting on normally flammable surfaces	Luminaire light beam spread	88°
ENEC mark	ENEC mark	Unified glare rating CEN	22

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	19.2 W
Power Factor (Fraction)	0.90
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	-
Overall height	208 mm
Overall diameter	218 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Dimensional drawing

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	1 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable
Product Data	
Order product name	DN470T LED20S/840 PSED D22H16 5C6 WH
Full product name	DN470T LED20S/840 PSED D22H16 5C6 WH
Full product code	871869938954300
Order code	912500100274
Material Nr. (12NC)	912500100274
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699389543
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699389543

