



# GreenSpace

## DN470T LED20S/840 PSU D22H16 3C GR

GreenSpace, 19.2 W, 2225 lm, 4000 K

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable colour performance and high colour rendering. The product's long lifetime makes it a true 'fit and forget' solution.

### Product data

General Information	
Lamp family code	LED20S [LED Module, system flux 2000 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical	
Luminous Flux	2,225 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	116 lm/W
Colour rendering index (CRI)	>80
Light source colour	840 neutral white
Optic type	-
Luminaire light beam spread	88°
Unified Glare Rating (CEN)	22

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.250 ms
Power Consumption	19.2 W
Power Factor (Fraction)	0.90
Connection	Connection unit 3-pole

Cable	-
Number of products on MCB of 16 A type B	34

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Plastic
Reflector material	Aluminium and polycarbonate
Optic material	-
Optical cover/lens material	-
Fixation material	-
Housing Colour	Grey
Optical cover/lens finish	-
Overall height	208 mm
Overall diameter	218 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	1 %
Control gear failure rate at median useful life	5 %
50,000 h	
Lumen maintenance at median useful life*	L90
50,000 h	
Lumen maintenance at median useful life*	L80
100,000 h	

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data

Order product name	DN470T LED20S/840 PSU D22H16 3C GR
Full product name	DN470T LED20S/840 PSU D22H16 3C GR
Full EOC	871869938956700
Order code	38956700
Material no. (12 NC)	912500100276
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718699389567
Numerator – packs per outer box	1
EAN/UPC - Case	8718699389567

Dimensional drawing



