



GreenSpace

DN470T LED20S/840 PSED D22H16 5C6 GR

GreenSpace, 19.2 W, 2225 lm, 4000 K, DALI

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information		Light Technical	
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Luminous Flux	2,225 lm
Cap-Base	- [-]	Correlated Color Temperature (Nom)	4000 K
Light source replaceable	No	Luminous Efficacy (rated) (Nom)	116 lm/W
Number of gear units	1 unit	Color rendering index (CRI)	>80
Driver included	Yes	Number of light sources	1
Lighting Technology	LED	Light source color	840 neutral white
Value ladder	Specification	Optic type	-
CE mark	Yes	Luminaire light beam spread	88°
Warranty period	5 years	Unified glare rating CEN	22
Flammability mark	For mounting on normally flammable surfaces		
ENEC mark	ENEC mark		
Glow-wire test	Temperature 650 °C, duration 5 s		
EU RoHS compliant	Yes		

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	19.2 W
Power Factor (Fraction)	0.90
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	Grey
Optical cover finish	-
Overall height	208 mm
Overall diameter	218 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

Product Data

Order product name	DN470T LED20S/840 PSED D22H16 5C6 GR
Full product name	DN470T LED20S/840 PSED D22H16 5C6 GR
Full product code	871869938958100
Order code	912500100278
Material Nr. (12NC)	912500100278
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699389581
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699389581

