



GreenSpace

DN460B LED11S/840 PSU-E C WH P

GreenSpace, 10.2 W, D150 mm, 1300 lm, 4000 K, High-gloss reflector, IP20

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

Product data

| General Information | | Service tag | Yes |
|--------------------------|---|---------------------|----------------------------------|
| Lamp family code | LED11S [LED Module, system flux 1100 lm] | Product family code | DN460B [150mm] |
| Light source replaceable | No | Lighting Technology | LED |
| Number of gear units | 1 unit | Value ladder | Specification |
| Gear | - | CE mark | Yes |
| Driver included | Yes | Warranty period | 5 years |
| Remarks | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | Flammability mark | - |
| | | ENEC mark | ENEC mark |
| | | Glow-wire test | Temperature 750 °C, duration 5 s |
| | | EU RoHS compliant | Yes |

| | |
|------------------------------------|-------------------|
| Light Technical | |
| Luminous Flux | 1,300 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 127 lm/W |
| Color rendering index (CRI) | >80 |
| Number of light sources | 1 |
| Beam angle of light source | - degree(s) |
| Light source color | 840 neutral white |
| Optic type | - |
| Luminaire light beam spread | 120° |
| Unified glare rating CEN | 22 |

| | |
|--|-------------------------------|
| Operating and Electrical | |
| Input Voltage | 220-240 V |
| Line Frequency | 50 to 60 Hz |
| Initial CLO power consumption | - W W |
| Average CLO power consumption | - W W |
| Inrush current | 14 A |
| Inrush time | 0.130 ms |
| Power Consumption | 10.2 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Feed-through connector 3-pole |
| Cable | - |
| Number of products on MCB of 16 A type B | 65 |

| | |
|---------------------------|---------------|
| Temperature | |
| Ambient temperature range | +10 to +40 °C |

| | |
|-------------------------------|-------------------------------------|
| Controls and Dimming | |
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit external (On/Off) |
| Control interface | - |
| Constant light output | No |

| | |
|------------------------|-------------------------------|
| Mechanical and Housing | |
| Housing Material | Polycarbonate |
| Reflector material | Polycarbonate aluminum coated |
| Optic material | Polycarbonate |
| Optical cover material | - |
| Fixation material | - |
| Housing Color | White |
| Optical cover finish | - |

| | |
|------------------|----------------------|
| Reflector Finish | High-gloss reflector |
| Overall height | 77 mm |
| Overall diameter | 166 mm |

| | |
|------------------------------|--------------------------|
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Sustainability rating | Lighting for circularity |
| Protection class IEC | Safety class II |

| | |
|-------------------------------------|---------------------|
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.38, 0.38) SDCM<3 |
| Power consumption tolerance | +/-10% |

| | |
|---|-----|
| Over Time Performance (IEC Compliant) | |
| Driver failure rate at 5000 h | 1 % |
| Control gear failure rate at median useful life 50000 h | 5 % |
| Lumen maintenance at median useful life* 50000 h | L90 |
| Lumen maintenance at median useful life* 100000 h | L80 |

| | |
|------------------------------------|----------------|
| Application Conditions | |
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level | Not applicable |
| Suitable for random switching | Yes |

| | |
|---------------------------------|--------------------------------|
| Product Data | |
| Order product name | DN460B LED11S/840 PSU-E C WH P |
| Full product name | DN460B LED11S/840 PSU-E C WH P |
| Full product code | 871869979320300 |
| Order code | 912500100515 |
| Material Nr. (12NC) | 912500100515 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718699793203 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8718699793203 |

Dimensional drawing

