

# HID ignitors for series systems

## SI 51 220-240V 50/60HZ

Electronic ignitors for HID lamps


### Product data

|                           |                 |
|---------------------------|-----------------|
| Operating and Electrical  |                 |
| Input Voltage             | 220 to 240 V    |
| Line Frequency            | 50 to 60 Hz     |
| Input Frequency           | 50 to 60 Hz     |
| Wiring                    |                 |
| Connector Type            | Screw           |
| Temperature               |                 |
| Ambient temperature range | -20 °C to 75 °C |
| T-Case Maximum (Max)      | 80 °C           |
| Mechanical and Housing    |                 |
| Housing                   | SNI-85          |

|                                 |                             |
|---------------------------------|-----------------------------|
| Approval and Application        |                             |
| Approval Marks                  | CE marking ENEC certificate |
| Product Data                    |                             |
| Order product name              | SI 51 220-240V 50/60Hz      |
| Full product name               | SI 51 220-240V 50/60HZ      |
| Full product code               | 871150091553530             |
| Order code                      | 91553530                    |
| Material Nr. (12NC)             | 913619519966                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 8711500915535               |
| Numerator - Packs per outer box | 48                          |
| EAN/UPC - Case                  | 8711500908353               |

# HID ignitors for series systems

## Dimensional drawing



| Product                | D1     | C1      | A1      | A2      | B1      |
|------------------------|--------|---------|---------|---------|---------|
| SI 51 220-240V 50/60Hz | 4.3 mm | 38.0 mm | 84.5 mm | 65.0 mm | 41.0 mm |

