

# HID-Constant wattage BSX for SOX

## BSX 180 H96 220-240V 50Hz CW-178/78


Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

### Product data

Operating and Electrical		Full product name		BSX 180 H96 220-240V 50Hz CW-178/78	
Input Voltage	220 to 240 V	Full product code		871150093900599	
Line Frequency	50 Hz	Order code		913626027226	
Input Frequency	50 Hz	Material Nr. (12NC)		913626027226	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8711500939005	
		Numerator - Packs per outer box		4	
		EAN/UPC - Case		8711500932167	
Approval and Application					
Approval Marks		CE marking ENEC certificate			
Product Data					
Order product name		BSX 180 H96 220-240V 50Hz CW-178/78			

# HID-Constant wattage BSX for SOX

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 180 H96 220-240V 50Hz CW-178/78	4.2 mm	78.0 mm	178.0 mm	162.0 mm	100.0 mm	42.0 mm

