

HID-Constant wattage BSX for SOX

BSX 55 H26 220-230V 50Hz CW-173/44

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps


Product data

Operating and Electrical	
Input Voltage	220 to 230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSX 55 H26 220-230V 50Hz CW-173/44

Full product name	BSX 55 H26 220-230V 50Hz CW-173/44
Full product code	871150091996099
Order code	91996099
Material Nr. (12NC)	913653000326
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500919960
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500932129

HID-Constant wattage BSX for SOX

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 55 H26 220-230V	4.2 mm	44.0 mm	173.0 mm	157.0 mm	64.0 mm	42.0 mm
50Hz CW-173/44						

