



# HID-Constant wattage BSX for SOX

## BSX 91 H96 220-240V 50Hz CW-149/67


Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSX 91 H96 220-240V 50Hz CW-149/67	
Input Voltage	220 to 240 V	<b>Full EOC</b>		871150092039399	
Line Frequency	50 Hz	<b>Order code</b>		92039399	
Input frequency	50 Hz	<b>Material no. (12 NC)</b>		913668007226	
		<b>Local order code</b>		BSX91H96	
<b>Wiring</b>		<b>SAP numerator – quantity per pack</b>		1	
Connector type	Screw	<b>EAN/UPC — Product/Case</b>		8711500920393	
		<b>Numerator – packs per outer box</b>		8	
<b>Approval and Application</b>		<b>EAN/UPC - Case</b>		8711500932242	
Approval marks	CE marking ENEC certificate				
<b>Product Data</b>					
Order product name	BSX 91 H96 220-240V 50Hz CW-149/67				

# HID-Constant wattage BSX for SOX

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 91 H96 220-240V 50Hz CW-149/67	4.2 mm	67.0 mm	149.0 mm	135.0 mm	80.0 mm	42.0 mm

