

LuxSense

LRL1220 TL5


LuxSense is a DayLight Regulation option (DLR) for luminaires equipped with a Philips HFR ballast. The sensor measures the reflected light coming from the surface below. It dims down the lamp output when the light level exceeds the required light level defined by the light sensor set point. LuxSense can be installed in the luminaire by attaching it to the lamp with a lamp clip. LuxSense is available as a complete set with a sensor and a lamp clip: LRL1220 TL-D for TLD lamps and LRL1220 TL5 for T5 lamps.

Product data

Product Data	
Order product name	LRL1220 TL5
Full product name	LRL1220 TL5
Full product code	871155967010230
Local code description	LRL1220TL5
Order code	913700182182
Material Nr. (12NC)	913700182182

Local order code	.
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559670102
Numerator - Packs per outer box	100
EAN/UPC - Case	8711559670119

Dimensional drawing



Product
LRL1220 TL5

