

LuxSense

LRL1220TLDI


LuxSense is a DayLight Regulation option (DLR) for luminaires equipped with a Philips HFR ballast. The sensor measures the reflected light coming from the surface below. It dims down the lamp output when the light level exceeds the required light level defined by the light sensor set point. LuxSense can be installed in the luminaire by attaching it to the lamp with a lamp clip. LuxSense is available as a complete set with a sensor and a lamp clip: LRL1220 TL-D for TLD lamps and LRL1220 TL5 for T5 lamps.

Product data

Product Data	
Order product name	LRL1220 TL-D
Full product name	LRL1220TLDI
Full product code	871155967012630
Local code description	LRL1220TLD
Order code	120188
Material Nr. (12NC)	913700182282

Local order code	120188
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559670126
Numerator - Packs per outer box	100
EAN/UPC - Case	8711559670133

Dimensional drawing



Product
LRL1220 TL-D

