



# HID-Basic BSX for SOX

## BSX 35/55 L82 240V 50Hz BC0-196

Impregnated electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps


### Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Insert
Approval and Application	
Approval marks	CE marking ENEC certificate
Product Data	
Order product name	BSX 35/55 L82 240V 50Hz BC0-196

Full product name	BSX 35/55 L82 240V 50Hz BC0-196
Full EOC	871150092053930
Order code	92053930
Material no. (12 NC)	913700200926
Local order code	BSX3555L82
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500920539
Numerator – packs per outer box	24
EAN/UPC - Case	8711500944115

HID-Basic BSX for SOX

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BSX 35/55	4.2	28.0	1.5	196.0	180.0	54.0	54.0	39.0	20.0
L82 240V	mm	mm	mm	mm	mm	mm	mm	mm	mm
50Hz									
BC0-196									

