



HID-HighPower for SON/MH/HPL/HPI

BHL 2000 L76 380/400/415V 50HZ HP-317

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

Product data

Operating and Electrical	
Input Voltage	380 to 415 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw


Approval and Application	
Approval Marks	CE marking ENEC certificate

Product Data	
Order product name	BHL 2000 L76-A2 380/400/415V 50Hz HP-317

Full product name	BHL 2000 L76 380/400/415V 50HZ HP-317
Full product code	871150006384700
Order code	06384700
Material Nr. (12NC)	913700217903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500996664
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500063847

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BHL 2000 L76-A2	6.5	102.0	317.0	282.0	306.0	117.0	88.0
380/400/415V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

