



# HID-HighPower for SON/MH/HPL/HPI

## BHD 2000 L76 380/400/415V 50Hz HP-317

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above


### Product data

Operating and Electrical	
Input Voltage	380 to 415 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Approval and Application	
Approval marks	CE marking ENEC certificate
Product Data	
Order product name	BHD 2000 L76-A2 380/400/415V 50Hz HP-317

Full product name	BHD 2000 L76 380/400/415V 50Hz HP-317
Full EOC	871150074276600
Order code	74276600
Material no. (12 NC)	913700232103
Local order code	BHD2000L76
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500996695
Numerator – packs per outer box	1
EAN/UPC – Case	8711500742766

# HID-HighPower for SON/MH/HPL/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BHD 2000 L76-A2	6.5	102.0	317.0	282.0	306.0	117.0	88.0
380/400/415V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

