



HID-HighPower for SON/MH/HPL/HPI

BHD 2000 L76-A2 380/400/415V 50Hz HP-317

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

Product data


General Information		Connector Type	
Application Code	L76-A2	Connector Type	Screw
Design	HP-317	System characteristics	
Lamp Type	MH	Capacitor	75µF/450V
Number of Lamps	1 piece/unit	Rated Ballast-Lamp Power	2000 W
Operating and Electrical		Recommended Ignitor	Series ignitor
Input Voltage	380 to 415 V	Temperature	
Input Frequency	50 Hz	T-Storage (Max)	80 °C
Input Voltage (Multi-Tab)	380/400/415	T-Storage (Min)	-25 °C
Power Factor 100% Load (Nom)	0.87	T-Winding (Max)	130 °C
Mains Voltage Performance (AC)	-8%+6%	Delta-T Normal Conditions	65 °C
Mains Voltage Safety (AC)	-10%+10%	Approval and Application	
Input Current with PF Correction	6.60 A	Approval Marks	CE marking ENEC certificate
Input Current without PF Correction	11.30 A	Product Data	
Power Factor without PF Compensation (Nom)	0.50	Full product code	871150074276600
Power Losses (Nom)	80.0 W	Order product name	BHD 2000 L76-A2 380/400/415V 50Hz HP-317
Wiring		EAN/UPC - Product	8711500996695
Wire Striplength	7.0 mm	Order code	913700232103
Ballast Contact Wire Cross Section	0.70-6.00 mm²		

HID-HighPower for SON/MH/HPL/HPI

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700232103

Net Weight (Piece)	17.500 kg
--------------------	-----------

Dimensional drawing



BHD 2000 L76 380/400/415V 50Hz HP-317

Product	D1	C1	A1	A2	A3	B1	B2
BHD 2000 L76-A2	6.5	102.0	317.0	282.0	306.0	117.0	88.0
380/400/415V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

