



# HID-Basic BHL MK4 for HPL/HPI

## BHL 250 K307 230/240V 50Hz BC2-134


Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>	BHL 250 K307 230/240V 50Hz BC2-134
Input Voltage	230 V (default) or 240 V	Full EOC	872790088701300
Line Frequency	50 Hz	Order code	88701300
Input frequency	50 Hz	Material no. (12 NC)	913700278026
<b>Wiring</b>		Local order code	BHL250K307
Connector type	Screw	SAP numerator – quantity per pack	1
<b>Approval and Application</b>		EAN/UPC – Product/Case	8711500881588
Approval marks	CE marking ENEC certificate	Numerator – packs per outer box	6
<b>Product Data</b>		EAN/UPC - Case	8727900887013
Order product name	BHL 250 K307-A2 230/240V 50Hz BC2-134		

# HID-Basic BHL MK4 for HPL/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 K307-A2 230/240V 50Hz	6.2 mm	65.0 mm	134.0 mm	113.0 mm	76.0 mm
BC2-134					

