



HID-Basic BHL MK4 for HPL/HPI

BHL 400 K307 230/240V 50Hz BC2-160


Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

Product data

Operating and Electrical		Full product name	BHL 400 K307 230/240V 50Hz BC2-160
Input Voltage	230 V (default) or 240 V	Full EOC	872790088703700
Line Frequency	50 Hz	Order code	88703700
Input frequency	50 Hz	Material no. (12 NC)	913700278226
Wiring		Local order code	BHL400K307
Connector type	Screw	SAP numerator – quantity per pack	1
Approval and Application		EAN/UPC – Product/Case	8711500881595
Approval marks	CE marking ENEC certificate	Numerator – packs per outer box	6
Product Data		EAN/UPC - Case	8727900887037
Order product name	BHL 400 K307-A2 230/240V 50Hz BC2-160		

HID-Basic BHL MK4 for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400 K307-A2 230/240V 50Hz	6.2 mm	65.0 mm	160.0 mm	139.0 mm	76.0 mm
BC2-160					

