

HID-Basic BHL for HPL/HPI

BHL 125 K202 230V 50Hz BC1-118


Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

Product data

Operating and Electrical		Full product name		BHL 125 K202 230V 50Hz BC1-118
Input Voltage	230 V	Full product code		872790094003900
Line Frequency	50 Hz	Order code		913700285926
Input Frequency	50 Hz	Material Nr. (12NC)		913700285926
		Numerator - Quantity Per Pack		1
Wiring		EAN/UPC - Product/Case		8727900940039
Connector Type	Screw	Numerator - Packs per outer box		6
		EAN/UPC - Case		8727900940046
Approval and Application				
Approval Marks	CE marking ENEC certificate			
Product Data				
Order product name	BHL 125 K202 230V 50Hz BC1-118			

HID-Basic BHL for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125 K202 230V 50Hz BC1-118	6.2 mm	52.0 mm	118.0 mm	94.0 mm	61.0 mm

