

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 70 K301-ITS 220V 60Hz BC1-118


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	BSN 70 K301-ITS 220V 60Hz BC1-118	
Line Frequency	60 Hz	Full product code	
Input Frequency	60 Hz	871829117724100	
Wiring		Order code	
Connector Type	Screw	913700293026	
Approval and Application		Material Nr. (12NC)	
Approval Marks	CE marking	913700293026	
Product Data		Numerator - Quantity Per Pack	
Order product name	BSN 70 K301-ITS 220V 60Hz BC1-118	1	
		EAN/UPC - Product/Case	
		8718291177241	
		Numerator - Packs per outer box	
		6	
		EAN/UPC - Case	
		8718291177258	

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70 K301-ITS 220V 60Hz BC1-118	6.2 mm	52.0 mm	118.0 mm	94.0 mm	61.0 mm

