



# OccuSwitch

## LRM1070/00 Sensr Mov Det St

Movement detector with a built-in switch - up to 6 A - controls max 25 m<sup>2</sup> area - Basic


Movement detector with a built-in switch - up to 6 A - controls max 25 m<sup>2</sup> area - Basic

### Product data

Product Data	
Full product code	871155973138499
Order product name	LRM1070/00 SENSr MOV DET ST
EAN/UPC - product	8711559731384
Order code	73138499
Numerator - quantity per pack	1

Numerator - packs per outer box	42
Material no. (12NC)	913700327803
Net weight (piece)	0.200 kg

### Dimensional drawing



LRM1070/00 SENSr MOV DET ST