



OccuSwitch

LRM1070/00 SENSr MOV DET ST

The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

Product data

Product Data	
Order product name	LRM1070/00 SENSr MOV DET ST
Full product name	LRM1070/00 SENSr MOV DET ST
Full product code	871155973138499
Local code description	LRM1070
Order code	913700327803
Material Nr. (12NC)	913700327803

Local order code	LRM1070
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559731384
Numerator - Packs per outer box	42
EAN/UPC - Case	8711559731391

Dimensional drawing

