



# OccuSwitch

## LRM1070/00 SENSr MOV DET ST


Movement detector with a built-in switch - up to 6 A - controls max 25 m<sup>2</sup> area - Basic

Movement detector with a built-in switch - up to 6 A - controls max 25 m<sup>2</sup> area - Basic

### Product data

Product Data		Packaging	
Full product code	871155973138499	Numerator – packs per outer box	42
Order product name	LRM1070/00 SENSr MOV DET ST	Material no. (12NC)	913700327803
EAN/UPC – product	8711559731384	Net weight (piece)	0.200 kg
Order code	913700327803		
Numerator – quantity per pack	1		

### Dimensional drawing



LRM1070/00 SENSr MOV DET ST