



OccuSwitch

LRM1080/00 SENSr MOV DET ST IR

Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Advanced


Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Advanced

Product data

Product Data	
Full product code	871155973140799
Order product name	LRM1080/00 SENSr MOV DET ST IR
EAN/UPC - product	8711559731407
Order code	913700327903
Numerator - quantity per pack	1

Numerator - packs per outer box	42
Material no. (12NC)	913700327903
Net weight (piece)	0.200 kg

Dimensional drawing



Product
LRM1080/00 SENSr MOV DET ST IR

LRM1080/00 SENSr MOV DET ST IR