



ActiLume 1-10V

LRI1655/00 ActiLume 1-10V Sensor 100 Cm


ActiLume 1-10 V can be connected to the 1-10 V DC control input of an HF-R ballast.
ActiLume 1-10 V is calibrated for use in a standard office situation.

Product data

Product Data	
Order product name	LRI1655/00 ActiLume 1-10V Sensor 100 Cm
Full product name	LRI1655/00 ActiLume 1-10V Sensor 100 Cm
Full product code	872790094298900
Order code	913700339503
Material Nr. (12NC)	913700339503

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900942989
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900942996

Dimensional drawing



Product
LRI1655/00 ActiLume 1-10V Sensor 100 Cm