



Luminaire Based Accessoires

LCA8002/00 ActiLume clip TL5 set 50pce

Clip to be used for ActiLume multisensor, ActiLume Luminaire based extension sensor, ActiLume 1-10V sensor and the ActiLume MicroLuxSense . With this clip the sensor can be directly clicked on the TL5 lamp.

Clip to be used for ActiLume multisensor, ActiLume Luminaire based extension sensor, ActiLume 1-10V sensor and the ActiLume MicroLuxSense . With this clip the sensor can be directly clicked on the TL5 lamp.

Product data

Product Data		Numerator – packs per outer box	
Full product code	872790095294000		20
Order product name	LCA8002/00 ActiLume clip TL5 set 50pce	Material no. (12NC)	913700340803
EAN/UPC – product	8727900952957	Net weight (piece)	0.008 kg
Order code	95294000		
Numerator – quantity per pack	1		