



OccuSwitch

LRM1085/00 SENSOR MOV DET ST IR CH

Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Advanced - CH


Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Advanced - CH

Product data

Product Data	
Full product code	871829113928700
Order product name	LRM1085/00 SENSOR MOV DET ST IR CH
EAN/UPC - product	8718291139287
Order code	13928700
Numerator - quantity per pack	1

Numerator - packs per outer box	42
Material no. (12NC)	913700344770
Net weight (piece)	0.166 kg

Dimensional drawing



LRM1085/00 SENSOR MOV DET ST IR CH