



OccuSwitch

LRM1085/00 SENSOR MOV DET ST IR CH

The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling

Product data

Product Data	
Order product name	LRM1085/00 SENSOR MOV DET ST IR CH
Full product name	LRM1085/00 SENSOR MOV DET ST IR CH
Full product code	871829113928700
Order code	913700344770
Material Nr. (12NC)	913700344770

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291139287
Numerator - Packs per outer box	42
EAN/UPC - Case	8718291139294

Dimensional drawing

