




ActiLume MicroLuxSense

LRL1222/10 ActiLume MicroLuxSense

ActiLume MicroLuxSense is connected to the 1-10 V DC control input of the HFR ballast. ActiLume MicroLuxSense dims light down close to the minimum level of the ballast. ActiLume MicroLuxSense is calibrated for use in a standard office situation with 600 lux installed and 500 lux required.


Dados do produto

Dados do produto	
Nome de produto da encomenda	LRL1222/10 ActiLume MicroLuxSense
Nome do produto completo	LRL1222/10 ActiLume MicroLuxSense
Full EOC	871829115238500
Descrição do código local	SENSOR LRL1222/10ACTILUMEMICROLUXSENSE
Código de encomenda	913700346403
Nº do material (12NC)	913700346403
Código local	LRL 1222/10


Numerador — Quantidade por embalagem	1
EAN/UPC - produto/caixa	8718291152385
Numerador SAP — Embalagens por exterior	1
EAN/UPC - caixa	8718291152392

ActiLume MicroLuxSense

Desenho dimensional



Product
LRL1222/10 ActiLume MicroLuxSense



Product
LRL1222/10 ActiLume MicroLuxSense

