



OccuSwitch Wireless

LRM1765/10 OS Wireless Corridor sensor

A wide range of wireless sensors with movement detection to control an area of 20-25 m2. Battery-operated, with a typical lifetime of 8-10 years. The actuator can switch any load up to 6 A and can be located in the ceiling or corridor. OccuSwitch Wireless will switch the lights off in a room or area when it is vacated and so save up to 30% on electricity. A detachable mains wiring connector enables easy installation. Separate Wieland and CEE cables are available for even easier, faster and trouble-free installation. Up to 10 sensors and/or actuators can be combined in one parallel network. The maximum distance between the sensor and actuator is 10 meters (depending on the application). With the extended scope of OccuSwitch Wireless functionality (increased number of sensors and interoperable with wireless ActiLume range), all wireless devices should be from the same version (LRM/LRA/LLC XXXX/10 or higher).

Product data

Product Data	
Order product name	LRM1765/10 OS Wireless Corridor sensor
Full product name	LRM1765/10 OS Wireless Corridor sensor
Full product code	871829125065400
Order code	913700352003
Material Nr. (12NC)	913700352003
Local order code	LRM1765OSWCD

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291250654
Numerator - Packs per outer box	20
EAN/UPC - Case	8718291250661