

# ActiLume MicroLuxSense

## LRL1222/15 ActiLume MicroluxSense W


ActiLume MicroLuxSense is connected to the 1-10 V DC control input of the HFR ballast. ActiLume MicroLuxSense dims light down close to the minimum level of the ballast. ActiLume MicroLuxSense is calibrated for use in a standard office situation with 600 lux installed and 500 lux required.

### Product data

Product Data	
Order product name	LRL1222/15 ActiLume MicroluxSense W
Full product name	LRL1222/15 ActiLume MicroluxSense W
Full product code	871829175225700
Order code	75225700
Material Nr. (12NC)	913700354803

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291752257
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291752264

### Dimensional drawing



Product
LRL1222/15 ActiLume MicroluxSense W

ActiLume MicroLuxSense

Dimensional drawing

