



OccuSwitch

LRM1011/10 OS Mov Det incl P-Pack CS


The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m2. A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

Product data

Product Data	
Order product name	LRM1011/10 OS Mov Det incl P-Pack CS
Full product name	LRM1011/10 OS Mov Det incl P-Pack CS
Full product code	871869644209800
Order code	913700359303
Material Nr. (12NC)	913700359303


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696442098
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696442104

Dimensional drawing



Product
LRM1011/10 OS Mov Det incl P-Pack CS

Dimensional drawing



Product
LRM1011/10 OS Mov Det incl P-Pack CS

