



OccuSwitch

LRM1033/00 OS Mov Det Switch 2w WR DIN


The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

Product data

Product Data	
Order product name	LRM1033/00 OS Mov Det Switch 2w WR DIN
Full product name	LRM1033/00 OS Mov Det Switch 2w WR DIN
Full EOC	871869644227200
Order code	44227200
Material no. (12 NC)	913700359703

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696442272
Numerator – packs per outer box	1
EAN/UPC – Case	8718696442289

Dimensional drawing



Product
LRM1033/00 OS Mov Det Switch 2w WR DIN