



# OccuSwitch

## LRM1040/01 OS Mov Det IP54 240 dgr bl WS

The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling

### Product data

Product Data		Numerator - Quantity Per Pack	
Order product name	LRM1040/01 OS Mov Det IP54 240 dgr bl WS	EAN/UPC - Product/Case	8718696443682
Full product name	LRM1040/01 OS Mov Det IP54 240 dgr bl WS	Numerator - Packs per outer box	1
Full product code	871869644368200	EAN/UPC - Case	8718696443699
Order code	913700359803		
Material Nr. (12NC)	913700359803		