



ActiLume 1-10V

LRM1657/05 ActiLume 1-10V Ind Mov Sensor

The ActiLume 1-10 V system consists of a sensor and a SwitchBox (controller) designed for easy integration into luminaires. The sensor can work independently of the SwitchBox. In combination with the SwitchBox, the luminaire will be switched off when enough daylight is present and/or when no presence is detected. The ActiLume 1-10 V luminaire-based sensor enables daylight regulation and dimming when no presence is detected. The delay time can be customized between 1 and 30 minutes.


The ActiLume 1-10 V system consists of a sensor and a SwitchBox (controller) designed for easy integration into luminaires. The sensor can work independently of the SwitchBox. In combination with the SwitchBox, the luminaire will be switched off when enough daylight is present and/or when no presence is detected. The ActiLume 1-10 V luminaire-based sensor enables daylight regulation and dimming when no presence is detected. The delay time can be customized between 1 and 30 minutes.

Product data

Product Data		Numerator - Packs per outer box	
Full product code	871869652494700		192
Order product name	LRM1657/05 ActiLume 1-10V Ind Mov Sensor	Material Nr. (12NC)	913700369103
EAN/UPC - Product	8718696524947	Net Weight (Piece)	0.028 kg
Order code	913700369103		
Numerator - Quantity Per Pack	1		

ActiLume 1-10V

Dimensional drawing



LRM1657/05 ActiLume 1-10V Ind Mov Sensor

