



Luminaire Based Accessoires

LRM8140/00 ActiLume G2 RF Mov Sensor

Radio frequency (RF) radar motion detection sensor which is to be connected to an ActiLume Wireless DALI gen2 controller.

Radio frequency (RF) radar motion detection sensor which is to be connected to an ActiLume Wireless DALI gen2 controller.

Product data

| Product Data | | Numerator – packs per outer box | |
|-------------------------------|--------------------------------------|---------------------------------|--------------|
| Full product code | 871869656919100 | Numerator – packs per outer box | 12 |
| Order product name | LRM8140/00 ActiLume G2 RF Mov Sensor | Material no. (12NC) | 913700389103 |
| EAN/UPC – product | 8718696569191 | Net weight (piece) | 33.000 g |
| Order code | 913700389103 | | |
| Numerator – quantity per pack | 1 | | |