



HF-Matchbox Blue

HF-M BLUE 124 LH TL/TL5/PL-L 230-240V

Compact, lightweight, High Frequency electronic ballast for TL (4-18W), TL5 (14-28W) and compact fluorescent PL (5-24W) lamps


Product data

| Operating and Electrical | |
|--|-----------------|
| Input Voltage | 230 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Number of Products on MCB (16A Type B) (Nom) | 60 |
| Wiring | |
| Connector Type Input Terminals | Insert |
| Color Input Terminals | Orange |
| Color Output Terminals | Grey |
| Connector Type Output Terminals | Insert |
| Cable Length From Device to Lamp | 1.50 m |
| Temperature | |
| Ambient temperature range | -10 °C to 40 °C |
| T-Case Maximum (Max) | 75 °C |
| Mechanical and Housing | |
| Housing | LH |

| Approval and Application | |
|---------------------------------|---|
| Ingress protection code | IP20 [Finger-protected] |
| Approval Marks | F-Marking CE marking VDE certificate CB Certificate |
| Product Data | |
| Order product name | HF-M BLUE 124 LH TL/TL5/PL-L 230-240V |
| Full product name | HF-M BLUE 124 LH TL/TL5/PL-L 230-240V |
| Full product code | 871150053640230 |
| Order code | 53640230 |
| Material Nr. (12NC) | 913700418066 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500536402 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8711500536419 |

HF-Matchbox Blue

Dimensional drawing



| Product | A1 | A2 | B1 | C1 | D1 |
|---------------------------------------|--------|--------|-------|-------|--------|
| HF-M BLUE 124 LH TL/TL5/PL-L 230-240V | 187 mm | 180 mm | 22 mm | 22 mm | 4.4 mm |

| Product |
|---------------------------------------|
| HF-M BLUE 124 LH TL/TL5/PL-L 230-240V |

